

EVC324 Cut Sheet



AutomationDirect connection cable, M12 right-angle female to axial male, 4-pole, 10-36 VDC, PNP LED, PUR jacket, black, 3.2ft/1m cable length, IP67, IP68 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EVC324>

Technical Specifications

Brand	AutomationDirect
Item	Cable
Cable Type	Connection
Connection 1	M12 right-angle female
Connection 2	Axial male
Number of Poles	4
Voltage Rating	10-36 VDC
Indicator	PNP LED
Jacket Material	PUR
Jacket Color	Black
Cable Length	3.2ft/1m
IP Rating	IP67, IP68 and IP69K

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191684
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/EVC324.pdf>
See store item page for other formats.