

# EVP-CA-PL Cut Sheet



NITRA pneumatic manual valve, 2-port (3-way), 2-position, N.C., metal plunger, spring return, axial ports, (1) 5/32in (4mm) push-to-connect inlet(s), (1) 5/32in (4mm) push-to-connect outlet(s), (1) vent hole exhaust(s), Cv=0.13.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EVP-CA-PL>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Valve
<b>Working Fluid</b>	Air or inert gas
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	2-port (3-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Operator Type</b>	Metal plunger
<b>Action</b>	Spring return
<b>Body Material</b>	Aluminum
<b>Inlet Port</b>	(1) 5/32in (4mm) push-to-connect

<b>Outlet Port</b>	(1) 5/32in (4mm) push-to-connect
<b>Exhaust Port</b>	(1) vent hole
<b>Port Orientation</b>	Axial
<b>Stackable</b>	No
<b>Flow Coefficient</b>	0.13
<b>Maximum Operating Pressure</b>	145 psi (10 bar)
<b>Minimum Operating Pressure</b>	7 psi (0.5 bar)
<b>For Use With</b>	Pneumatic pushbutton operators

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/EVP-CA-PL.pdf>  
See store item page for other formats.