

# EVT433 Cut Sheet



AutomationDirect connection cable, M8 axial male to right-angle female, 4-pole, PVC jacket, orange, 1.9ft/0.6m cable length, IP65, IP67, IP68 and IP69K, suitable for food and beverage applications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EVT433>

## Technical Specifications

Brand	AutomationDirect
Item	Cable
Cable Type	Connection
Connection 1	M8 axial male
Connection 2	Right-angle female
Number of Poles	4
Jacket Material	PVC
Jacket Color	Orange
Cable Length	1.9ft/0.6m
IP Rating	IP65, IP67, IP68 and IP69K
Application	Suitable for food and beverage applications

## Agency Approvals

UL Listed File #	E191684
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/EVT433.pdf>  
See store item page for other formats.