

# F0-04THM Cut Sheet



DirectLOGIC DL05/06 temperature input module, thermocouple, 4-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F0-04THM>

## Technical Specifications

<b>Brand</b>	DirectLOGIC
<b>Item</b>	Input module
<b>I/O Module Type</b>	Temperature
<b>Series</b>	DL05/06
<b>Input Signal Type(s)</b>	Thermocouple
<b>Number Of Input Channels</b>	4
<b>Input Thermocouple Signal Type</b>	J, E, K, R, S, T, B, N, C
<b>Input Voltage Signal Range</b>	0-1.25 VDC, 0-39.0625 mVDC, +/- 39.0625 mVDC, +/- 78.125 mVDC, 0-156.25 mVDC, +/- 156 mVDC
<b>Input Resolution</b>	16-bit
<b>Programming Software</b>	DirectSOFT programming software v4.0 or later

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/F0-04THM.pdf>  
See store item page for other formats.