


F0-CP128 Cut Sheet



DirectLOGIC DL05/06 communication module, ASCII, 3 ports, buffered, 128k program memory, 100 MHz maximum switching frequency, (2) RS-232 and (1) RS-485 port(s). For use with DL05 and DL06 PLCs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F0-CP128>

Technical Specifications

Brand	DirectLOGIC
Item	Communication module
Series	DL05/06
Number of Ports	3
Buffered Ports	Yes
Program Memory	128k
Maximum Switching Frequency	100 MHz
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (2) RS-232• (1) RS-485
Port Protocol(s)	ASCII BASIC
Port Speed(s)	up to 115.2k baud
For Use With	DL05 and DL06 PLCs
Programming Software	DirectSOFT programming software v4.0 or later
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.04• Replacement Battery: BR1632• Generic Battery: BR1632

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document