

F0S06HP Cut Sheet

Eaton flange handle, lever, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 1/3R/12. For use with AutomationDirect (Eaton) 100A frame MCCBs. 6ft cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F0S06HP>



Technical Specifications

Brand	Eaton
Item	Handle
Handle Type	Flange
Handle Style	Lever
Mounting	External front
Number Of Positions	2
Lockable Positions	OFF only
Defeatable	Yes
NEMA Rating	1/3R/12
For Use With	AutomationDirect (Eaton) 100A frame MCCBs
Includes	6ft cable

Agency Approvals

UL Listed File #	E64983
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F0S06HP.pdf>
See store item page for other formats.