

F12020DN Cut Sheet

NITRA pneumatic cylinder, all stainless steel non-repairable, 3/4in bore, 1/4in rod diameter, 2in stroke, double acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F12020DN>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	All stainless steel non-repairable
Bore Diameter	3/4in
Stroke	2in
Port Size	1/8in female NPT
Mounting	Front nose
Action Type	Double acting
Body Material	Stainless steel
End Cap Material	Stainless steel
Rod Material	Stainless steel
Rod Diameter	1/4in
Rod Thread Size	1/4-28

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document