F17030DD-M Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic cylinder, all stainless steel non-repairable, 1-1/16in bore, 5/16in rod diameter, 3in stroke, double acting, magnetic piston, double end mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/F17030DD-M

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	All stainless steel non-repairable
Bore Diameter	1-1/16in
Stroke	3in
Port Size	1/8in female NPT
Mounting	Double end
Action Type	Double acting

Magnetic Piston	Yes
Adjustable Cushions	No
Body Material	Stainless steel
End Cap Material	Stainless steel
Rod Material	Stainless steel
Rod Diameter	5/16in
Rod Thread Size	5/16-24 UNF
Maximum Operating Pressure	250 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/F17030DD-M.pdf
See store item page for other formats.