

F17100DD Cut Sheet

NITRA pneumatic cylinder, all stainless steel non-repairable, 1-1/16in bore, 5/16in rod diameter, 10in stroke, double acting, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F17100DD>

Technical Specifications

| | |
|-------------------------|------------------------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air |
| Cylinder Type | All stainless steel non-repairable |
| Bore Diameter | 1-1/16in |
| Stroke | 10in |
| Port Size | 1/8in female NPT |
| Mounting | Double end |
| Action Type | Double acting |
| Body Material | Stainless steel |
| End Cap Material | Stainless steel |
| Rod Material | Stainless steel |
| Rod Diameter | 5/16in |
| Rod Thread Size | 5/16-24 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |