

F2-08TRS Cut Sheet



DirectLOGIC DL205 relay output module, 8-point, 12-24 VDC/12-240 VAC, (5) Form A (SPST) no-suppression, (3) Form C (SPDT) no-suppression, 8 isolated common(s), 1 point(s) per common, 7A/point max. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F2-08TRS>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL205
Number of Output Points	8
Nominal Output Voltage	12-24 VDC/12-240 VAC
Relay Configuration	(5) Form A (SPST) no-suppression relays, (3) Form C (SPDT) no-suppression relays
Number of Isolated Commons	8

Jumper Selectable Isolation	No
Number of Points per Common	1
Load Current	7A/point max
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	234884
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F2-08TRS.pdf>
See store item page for other formats.