

F25AW3 Cut Sheet



Eaton NEMA limit switch, 360 degree stainless steel rod, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 29.4mm x 60mm hole spacing, die-cast zinc, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F25AW3>

Technical Specifications

| | |
|-----------------------|--------------------------------|
| Brand | Eaton |
| Item | Limit switch |
| Switch Type | NEMA |
| Actuator Type | 360 degree stainless steel rod |
| Head Type | 90-degree adjustable |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 39mm |
| Mounting Hole Spacing | 29.4mm x 60mm |
| Material | Die-cast zinc |
| IP Rating | IP67 |
| Operating Temperature | -10 to 121 deg C |
| Connection | (1) 1/2in NPT cable entry |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E170645 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F25AW3.pdf>
See store item page for other formats.