

F25BSRL551 Cut Sheet



Eaton NEMA limit switch, side rotary 3in stainless steel lever with metal roller, 90-degree adjustable head, (2) N.O./(2) N.C. contact(s), snap action, 29.4mm x 60mm hole spacing, die-cast zinc, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F25BSRL551>

Technical Specifications

| | |
|------------------------------|---|
| Brand | Eaton |
| Item | Limit switch |
| Switch Type | NEMA |
| Actuator Type | Side rotary 3in stainless steel lever with metal roller |
| Head Type | 90-degree adjustable |
| Contact Type | (2) N.O./(2) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 39mm |
| Mounting Hole Spacing | 29.4mm x 60mm |
| Material | Die-cast zinc |
| IP Rating | IP67 |
| Operating Temperature | -12 to 94 deg C |
| Connection | (1) 1/2in NPT cable entry |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E170645 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |