

F25BTP1 Cut Sheet



Eaton NEMA limit switch, metal plunger, 90-degree adjustable head, (2) N.O./ (2) N.C. contact(s), snap action, 29.4mm x 60mm hole spacing, die-cast zinc, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F25BTP1>

Technical Specifications

Brand	Eaton
Item	Limit switch
Switch Type	NEMA
Actuator Type	Metal plunger
Head Type	90-degree adjustable
Contact Type	(2) N.O./ (2) N.C.
Action	Snap action
Reset	No
Body Width	39mm
Mounting Hole Spacing	29.4mm x 60mm
Material	Die-cast zinc
IP Rating	IP67
Operating Temperature	-10 to 94 deg C
Connection	(1) 1/2in NPT cable entry

Agency Approvals

UL Listed File #	E170645
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document