

# F25BW4 Cut Sheet



Eaton NEMA limit switch, 360 degree stainless steel spring, 90-degree adjustable head, (2) N.O./ (2) N.C. contact(s), snap action, 29.4mm x 60mm hole spacing, die-cast zinc, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F25BW4>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Limit switch
<b>Switch Type</b>	NEMA
<b>Actuator Type</b>	360 degree stainless steel spring
<b>Head Type</b>	90-degree adjustable
<b>Contact Type</b>	(2) N.O./ (2) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	39mm
<b>Mounting Hole Spacing</b>	29.4mm x 60mm
<b>Material</b>	Die-cast zinc
<b>IP Rating</b>	IP67
<b>Operating Temperature</b>	-10 to 121 deg C
<b>Connection</b>	(1) 1/2in NPT cable entry

## Agency Approvals

<b>UL Listed File #</b>	E170645
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>