

F32020DD-M Cut Sheet

NITRA pneumatic cylinder, all stainless steel non-repairable, 2in bore, 5/8in rod diameter, 2in stroke, double acting, magnetic piston, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F32020DD-M>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	All stainless steel non-repairable
Bore Diameter	2in
Stroke	2in
Port Size	1/4in female NPT
Mounting	Double end
Action Type	Double acting
Magnetic Piston	Magnetic piston
Body Material	Stainless steel
End Cap Material	Stainless steel
Rod Material	Stainless steel
Rod Diameter	5/8in
Rod Thread Size	1/2-20

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document