

# F32060DD-M Cut Sheet

NITRA pneumatic cylinder, all stainless steel non-repairable, 2in bore, 5/8in rod diameter, 6in stroke, double acting, magnetic piston, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F32060DD-M>

## Technical Specifications

|               |                                    |
|---------------|------------------------------------|
| Brand         | NITRA                              |
| Item          | Cylinder                           |
| Working Fluid | Air or inert gas                   |
| Cylinder Type | All stainless steel non-repairable |
| Bore Diameter | 2in                                |
| Stroke        | 6in                                |
| Port Size     | 1/4in female NPT                   |
| Mounting      | Double end                         |

|                  |                 |
|------------------|-----------------|
| Action Type      | Double acting   |
| Magnetic Piston  | Magnetic piston |
| Body Material    | Stainless steel |
| End Cap Material | Stainless steel |
| Rod Material     | Stainless steel |
| Rod Diameter     | 5/8in           |
| Rod Thread Size  | 1/2-20          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/F32060DD-M.pdf>  
See store item page for other formats.