

F32140DD Cut Sheet



NITRA pneumatic cylinder, all stainless steel non-repairable, 2in bore, 5/8in rod diameter, 14in stroke, double acting, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F32140DD>

Technical Specifications

| | |
|------------------|------------------------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | All stainless steel non-repairable |
| Bore Diameter | 2in |
| Stroke | 14in |
| Port Size | 1/4in female NPT |
| Mounting | Double end |
| Action Type | Double acting |
| Body Material | Stainless steel |
| End Cap Material | Stainless steel |
| Rod Material | Stainless steel |
| Rod Diameter | 5/8in |
| Rod Thread Size | 1/2-20 |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F32140DD.pdf>
See store item page for other formats.