

F4-04DA-1 Cut Sheet



DirectLOGIC DL405 analog output module, 4-channel, current, 12-bit, output current signal range(s) of 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-04DA-1>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Analog
Series	DL405
Number Of Output Channels	4
Output Signal Type	Current
Analog Output Type	Sinking
Isolated Channels	No

Number of Non-Isolated Output Commons	1
Output Resolution	12-bit
Output Current Signal Range	4-20 mA
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F4-04DA-1.pdf>
See store item page for other formats.