

F4-08RTD Cut Sheet



DirectLOGIC DL405 temperature input module, RTD, 8-channel, 16-bit resolution, input RTD type(s): Pt100, JPt100, Cu10, Cu25 and Pt1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08RTD>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Temperature
Series	DL405
Input Signal Type(s)	RTD
Number Of Channels	8
Input RTD Signal Types	Pt100, JPt100, Cu10, Cu25 and Pt1000
Input Resolution	16-bit
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F4-08RTD.pdf>
See store item page for other formats.