

# F4-08THM-J Cut Sheet



DirectLOGIC DL405 temperature input module, thermocouple, 8-channel, 12-bit resolution, input thermocouple type(s): J.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08THM-J>

## Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Temperature
Series	DL405
Input Signal Type(s)	Thermocouple
Number Of Input Channels	8
Input Thermocouple Signal Type	J
Input Resolution	12-bit
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/F4-08THM-J.pdf>  
See store item page for other formats.