

F4-08THM-K Cut Sheet



DL405 temperature input module, thermocouple, 8-channel, 12-bit resolution, input thermocouple type(s): K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08THM-K>

Technical Specifications

Brand	DL405
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermocouple
Number Of Input Channels	8
Input Thermocouple Signal Type	K
Isolated Channels	No
Input Resolution	12-bit
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F4-08THM-K.pdf>
See store item page for other formats.