

F4-08THM-T Cut Sheet



DL405 temperature input module, thermocouple, 8-channel, 12-bit resolution, input thermocouple type(s): T.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-08THM-T>

Technical Specifications

Brand	DL405
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermocouple
Number Of Input Channels	8
Input Thermocouple Signal Type	T
Isolated Channels	No
Input Resolution	12-bit
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/F4-08THM-T.pdf>
See store item page for other formats.