

F4-16AD-1 Cut Sheet



DirectLOGIC DL405 analog input module, 16-channel, current, 12-bit, input current signal range(s) of 0-20 mA, 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-16AD-1>

Technical Specifications

| | |
|---|---|
| Brand | DirectLOGIC |
| Item | Input module |
| I/O Module Type | Analog |
| Series | DL405 |
| Number Of Input Channels | 16 |
| Input Signal Type(s) | Current |
| Analog Input Type | Sinking |
| Isolated Channels | No |
| Number of Non-Isolated Input Commons | 1 |
| Input Resolution | 12-bit |
| Input Current Signal Range | 0-20 mA, 4-20 mA |
| External Power Requirement | 24 VDC |
| Programming Software | DirectSOFT programming software v4.0 or later |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |