

F4-16AD-2 Cut Sheet



DirectLOGIC DL405 analog input module, 16-channel, voltage, 12-bit, input voltage signal range(s) of 0-5 VDC, 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-16AD-2>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Analog
Series	DL405
Number Of Input Channels	16
Input Signal Type(s)	Voltage
Isolated Channels	No
Number of Non-Isolated Input Commons	1
Input Resolution	12-bit
Input Voltage Signal Range	0-5 VDC, 0-10 VDC
External Power Requirement	24 VDC
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
RoHS Status	No
EU REACH	View EU REACH document