

# F4-CP128-1 Cut Sheet



DirectLOGIC DL405 communication module, ASCII, 3 ports, buffered, 128k program memory, 26 MHz maximum switching frequency, (1) RS-232 and (2) RS-232/RS-422/RS-485 port(s). For use with all DL405 PLCs. Commander programming software CD-ROM for Windows included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-CP128-1>

## Technical Specifications

<b>Brand</b>	DirectLOGIC
<b>Item</b>	Communication module
<b>Series</b>	DL405
<b>Number of Ports</b>	3
<b>Buffered Ports</b>	Yes
<b>Program Memory</b>	128k
<b>Maximum Switching Frequency</b>	26 MHz
<b>Communication Port and Connection Type(s)</b>	<ul style="list-style-type: none"><li>• (1) RS-232</li><li>• (2) RS-232/RS-422/RS-485</li></ul>
<b>Port Protocol(s)</b>	ASCII BASIC
<b>Port Speed(s)</b>	up to 115.2k baud

<b>For Use With</b>	All DL405 PLCs
<b>Includes</b>	Commander programming software CD-ROM for Windows
<b>Programming Software</b>	DirectSOFT programming software v4.0 or later
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Battery Installed: Yes</li><li>• Packaging Instructions: 970</li><li>• UN Number: UN3091</li><li>• Hazard Type: Lithium Batteries</li><li>• Battery Type: Button</li><li>• Lithium Content: 0.01</li><li>• Replacement Battery: BR1225</li><li>• Generic Battery: BR1225</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/F4-CP128-1.pdf>  
See store item page for other formats.