

F4E Cut Sheet



Minerallac flange mount cable clip, package of 100. For use with 3/16 to 9/32in flanges and 0.500-0.718in OD tubing or cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4E>

Technical Specifications

Brand	Minerallac
Item	Cable clip
Mount Type	Flange mount
Material	High carbon steel (HCS)
Finish	Zinc plated
Minimum Flange Thickness	3/16in
Maximum Flange Thickness	9/32in
Outside Diameter	0.500-0.718in
Tubing Size	1/2in, 9/16in, 5/8in and 11/16in
Electrical Metallic Tubing (EMT) Trade Size	1/2in
Reduced Wall Flexible Metal Conduit Trade Size	3/8in
Quantity per Pack	100
For Use With	3/16 to 9/32in flanges and 0.500-0.718in OD tubing or cable

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document