

F4F Cut Sheet



Minerallac flange mount cable clip, package of 100. For use with 3/16 to 9/32in flanges and 0.750-0.937in OD tubing or cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4F>

Technical Specifications

Brand	Minerallac
Item	Cable clip
Mount Type	Flange mount
Material	High carbon steel (HCS)
Finish	Zinc plated
Minimum Flange Thickness	3/16in
Maximum Flange Thickness	9/32in
Outside Diameter	0.750-0.937in
Tubing Size	3/4in, 13/16in, 7/8in and 15/16in
Rigid Metallic Conduit (RMC) Trade Size	1/2in

Electrical Metallic Tubing (EMT) Trade Size	3/4in
Intermediate Metallic Conduit (IMC) Trade Size	1/2in
Reduced Wall Flexible Metal Conduit Trade Size	1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in
Quantity per Pack	100
For Use With	3/16 to 9/32in flanges and 0.750-0.937in OD tubing or cable

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document