

F8R6-LP-1F Cut Sheet



ProSense photoelectric sensor, tubular, threaded, diffuse, visible red light emission, 1-60mm sensing distance, light-on, PNP, 500 Hz switching frequency, stainless steel housing, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F8R6-LP-1F>

Technical Specifications

Brand	ProSense
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	8mm diameter x 40mm body
IP Rating	IP67
Housing Material	Stainless steel
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Number of Wires	3
Switching Output	PNP
Sensing Distance	1-60mm
Operation Mode	Light-on
Switching Frequency	500 Hz
Light emission	Visible red
IO-Link Compatible	No
Connection	3-pin M8 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document