

FA-DCDC-1 Cut Sheet



AutomationDirect DC to DC converter, 12-24 VDC input, +/- 10 VDC, +/-5 VDC output, 0.125A, 3.75W, plastic housing, 35mm DIN rail mount, screw terminal, removable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FA-DCDC-1>

Technical Specifications

Brand	AutomationDirect
Item	DC to DC converter
Input voltage range	12-24 VDC
Output Voltage Range	+/- 10 VDC, +/-5 VDC
Load Current	0.125A
Output Power	3.75W
Housing Material	Plastic
Encapsulated	No
Mounting	35mm DIN rail
Terminal Block Type	Screw terminal
Removable	Yes
Number of Isolated Commons	2

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document