

FA-GFCI Cut Sheet



AutomationDirect duplex-receptacle outlet, 15A combined, 125 VAC, ground-fault circuit interruption protection, 35mm DIN rail mount, for laptop computers and test equipment.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FA-GFCI>

Technical Specifications

Brand	AutomationDirect
Item	Duplex-receptacle outlet
Amperage Rating	15A combined
Voltage Rating	125 VAC
Protection Type(s)	ground-fault circuit interruption
Mounting	35mm DIN rail
Application	For laptop computers and test equipment

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document