

# FALN-BP-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, polarized retroreflective, Class 1 red laser, 0.06-30m sensing distance, complementary light-on/dark-on, PNP, potentiometer, 4-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FALN-BP-0E>

## Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Polarized retroreflective
Operating Voltage	10-30 VDC
Number of Wires	4

Switching Output	PNP
Sensing Distance	0.06-30m
Sensitivity	Potentiometer
Operation Mode	Complementary light-on/dark-on
Switching Frequency	800 Hz
Light Emission (NP)	Class 1 red laser
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>