

FAZ-B15-1-NA-L-SP Cut Sheet



Eaton miniature circuit breaker, current-limiting, 15A, 240 VAC / 48 VDC, 1-pole, B curve, thermal magnetic, 14kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B15-1-NA-L-SP>

Technical Specifications

| | |
|---------------------------------|-------------------|
| Brand | Eaton |
| Item | Circuit breaker |
| Circuit Breaker Type | Miniature |
| Circuit Type | Feeder and branch |
| Current-Limiting | Yes |
| Amperage Rating | 15A |
| Voltage Rating | 240 VAC / 48 VDC |
| Number of Poles | 1 |
| Trip Curve | B curve |
| Trip Type | Thermal magnetic |
| Interrupting Rating | 14kA @ 240 VAC |
| UL Rating | UL 489 listed |
| Mounting | 35mm DIN rail |
| HACR Rated | Yes |
| Reverse Feed Capable | Yes |
| Manufacturer Part Number | FAZ-B15/1-NA-L-SP |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E235139 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 204453 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |