

# FAZ-B20-1-NA-L-SP Cut Sheet



Eaton miniature circuit breaker, current-limiting, 20A, 240 VAC / 48 VDC, 1-pole, B curve, thermal magnetic, 14kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B20-1-NA-L-SP>

## Technical Specifications

|                                 |                   |
|---------------------------------|-------------------|
| <b>Brand</b>                    | Eaton             |
| <b>Item</b>                     | Circuit breaker   |
| <b>Circuit Breaker Type</b>     | Miniature         |
| <b>Circuit Type</b>             | Feeder and branch |
| <b>Current-Limiting</b>         | Yes               |
| <b>Amperage Rating</b>          | 20A               |
| <b>Voltage Rating</b>           | 240 VAC / 48 VDC  |
| <b>Number of Poles</b>          | 1                 |
| <b>Trip Curve</b>               | B curve           |
| <b>Trip Type</b>                | Thermal magnetic  |
| <b>Interrupting Rating</b>      | 14kA @ 240 VAC    |
| <b>UL Rating</b>                | UL 489 listed     |
| <b>Mounting</b>                 | 35mm DIN rail     |
| <b>HACR Rated</b>               | Yes               |
| <b>Reverse Feed Capable</b>     | Yes               |
| <b>Manufacturer Part Number</b> | FAZ-B20/1-NA-L-SP |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E235139                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 204453                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |