

# FAZ-B20-1-SP Cut Sheet



Eaton miniature supplementary protector, 20A, 277 VAC / 48 VDC, 1-pole, B curve, thermal magnetic, 10kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B20-1-SP>

## Technical Specifications

|                      |                         |
|----------------------|-------------------------|
| Brand                | Eaton                   |
| Item                 | Supplementary protector |
| Circuit Breaker Type | Miniature               |
| Circuit Type         | Supplementary           |
| Current-Limiting     | No                      |
| Amperage Rating      | 20A                     |
| Voltage Rating       | 277 VAC / 48 VDC        |
| Number of Poles      | 1                       |

|                          |                    |
|--------------------------|--------------------|
| Trip Curve               | B curve            |
| Trip Type                | Thermal magnetic   |
| Interrupting Rating      | 10kA @ 277 VAC     |
| UL Rating                | UL 1077 recognized |
| Mounting                 | 35mm DIN rail      |
| HACR Rated               | No                 |
| Reverse Feed Capable     | Yes                |
| Manufacturer Part Number | FAZ-B20/1-SP       |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | E177451                                |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 204453                                 |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FAZ-B20-1-SP.pdf>  
See store item page for other formats.