

# FAZ-B4-2-NA-L Cut Sheet



Eaton miniature circuit breaker, current-limiting, 4A, 240 VAC / 96 VDC, 2-pole, B curve, thermal magnetic, 10kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B4-2-NA-L>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Circuit breaker
<b>Circuit Breaker Type</b>	Miniature
<b>Circuit Type</b>	Feeder and branch
<b>Current-Limiting</b>	Yes
<b>Amperage Rating</b>	4A
<b>Voltage Rating</b>	240 VAC / 96 VDC
<b>Number of Poles</b>	2
<b>Trip Curve</b>	B curve
<b>Trip Type</b>	Thermal magnetic
<b>Interrupting Rating</b>	10kA @ 240 VAC
<b>UL Rating</b>	UL 489 listed
<b>Mounting</b>	35mm DIN rail
<b>HACR Rated</b>	Yes
<b>Reverse Feed Capable</b>	Yes
<b>Manufacturer Part Number</b>	FAZ-B4/2-NA-L

## Agency Approvals

<b>UL Listed File #</b>	E235139
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	204453
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>