

FAZ-B40-2 Cut Sheet



Eaton miniature supplementary protector, 40A, 480Y / 277 VAC / 96 VDC, 2-pole, B curve, thermal magnetic, 5kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B40-2>

Technical Specifications

Brand	Eaton
Item	Supplementary protector
Circuit Breaker Type	Miniature
Circuit Type	Supplementary
Current-Limiting	No
Amperage Rating	40A
Voltage Rating	480Y / 277 VAC / 96 VDC
Number of Poles	2
Trip Curve	B curve
Trip Type	Thermal magnetic
Interrupting Rating	5kA @ 480Y/277 VAC
UL Rating	UL 1077 recognized
Mounting	35mm DIN rail
HACR Rated	No
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-B40/2

Agency Approvals

UL Listed File #	None
UL Recognized File #	E177451
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document