

# FAZ-B8-1-NA-SP Cut Sheet



Eaton miniature circuit breaker, current-limiting, 8A, 277 VAC / 48 VDC, 1-pole, B curve, thermal magnetic, 10kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-B8-1-NA-SP>

## Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	8A
Voltage Rating	277 VAC / 48 VDC
Number of Poles	1
Trip Curve	B curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 277 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-B8/1-NA-SP

## Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>