

FAZ-C20-2-NA Cut Sheet



Eaton miniature circuit breaker, current-limiting, 20A, 480Y / 277 VAC / 96 VDC, 2-pole, C curve, thermal magnetic, 14kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-C20-2-NA>

Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	20A
Voltage Rating	480Y / 277 VAC / 96 VDC
Number of Poles	2
Trip Curve	C curve
Trip Type	Thermal magnetic
Interrupting Rating	14kA @ 480Y/277 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-C20/2-NA

Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document