FAZ-C4-1-NA-L-SP Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Eaton miniature circuit breaker, current-limiting, 4A, 240 VAC/48 VDC, 1-pole, C curve, thermal magnetic, 10kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/FAZ-C4-1-NA-L-SP

Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	4A
Voltage Rating	240 VAC/48 VDC
Number of Poles	1

Trip Curve	C curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 240 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-C4/1-NA-L-SP

Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/FAZ-C4-1-NA-L-SP.pdf
See store item page for other formats.