

FAZ-C40-1-SP Cut Sheet



Eaton miniature supplementary protector, 40A, 277 VAC / 48 VDC, 1-pole, C curve, thermal magnetic, 5kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-C40-1-SP>

Technical Specifications

Brand	Eaton
Item	Supplementary protector
Circuit Breaker Type	Miniature
Circuit Type	Supplementary
Current-Limiting	No
Amperage Rating	40A
Voltage Rating	277 VAC / 48 VDC
Number of Poles	1

Trip Curve	C curve
Trip Type	Thermal magnetic
Interrupting Rating	5kA @ 277 VAC
UL Rating	UL 1077 recognized
Mounting	35mm DIN rail
HACR Rated	No
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-C40/1-SP

Agency Approvals

UL Listed File #	None
UL Recognized File #	E177451
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FAZ-C40-1-SP.pdf>
See store item page for other formats.