

FAZ-C5-2-NA-L Cut Sheet



Eaton miniature circuit breaker, current-limiting, 5A, 240 VAC / 96 VDC, 2-pole, C curve, thermal magnetic, 10kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-C5-2-NA-L>

Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	5A
Voltage Rating	240 VAC / 96 VDC
Number of Poles	2
Trip Curve	C curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 240 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-C5/2-NA-L

Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document