

# FAZ-D1-2-NA Cut Sheet



Eaton miniature circuit breaker, current-limiting, 1A, 480Y / 277 VAC / 96 VDC, 2-pole, D curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-D1-2-NA>

## Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	1A
Voltage Rating	480Y / 277 VAC / 96 VDC
Number of Poles	2

Trip Curve	D curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 480Y/277 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-D1/2-NA

## Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FAZ-D1-2-NA.pdf>  
See store item page for other formats.