

FAZ-D13-3-NA Cut Sheet



Eaton miniature circuit breaker, current-limiting, 13A, 480Y / 277 VAC / 96 VDC, 3-pole, D curve, thermal magnetic, 14kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-D13-3-NA>

Technical Specifications

| | |
|----------------------|-------------------------|
| Brand | Eaton |
| Item | Circuit breaker |
| Circuit Breaker Type | Miniature |
| Circuit Type | Feeder and branch |
| Current-Limiting | Yes |
| Amperage Rating | 13A |
| Voltage Rating | 480Y / 277 VAC / 96 VDC |
| Number of Poles | 3 |

| | |
|--------------------------|---------------------|
| Trip Curve | D curve |
| Trip Type | Thermal magnetic |
| Interrupting Rating | 14kA @ 480Y/277 VAC |
| UL Rating | UL 489 listed |
| Mounting | 35mm DIN rail |
| HACR Rated | Yes |
| Reverse Feed Capable | Yes |
| Manufacturer Part Number | FAZ-D13/3-NA |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E235139 |
| UL Recognized File # | None |
| CE | View CE declarations |
| CSA File # | 204453 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FAZ-D13-3-NA.pdf>
See store item page for other formats.