

FAZ-D13-3 Cut Sheet



Eaton miniature supplementary protector, 13A, 480Y / 277 VAC / 96 VDC, 3-pole, D curve, thermal magnetic, 5kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-D13-3>

Technical Specifications

Brand	Eaton
Item	Supplementary protector
Circuit Breaker Type	Miniature
Circuit Type	Supplementary
Current-Limiting	No
Amperage Rating	13A
Voltage Rating	480Y / 277 VAC / 96 VDC
Number of Poles	3

Trip Curve	D curve
Trip Type	Thermal magnetic
Interrupting Rating	5kA @ 480Y/277 VAC
UL Rating	UL 1077 recognized
Mounting	35mm DIN rail
HACR Rated	No
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-D13/3

Agency Approvals

UL Listed File #	None
UL Recognized File #	E177451
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FAZ-D13-3.pdf>
See store item page for other formats.