

FAZ-D2-3-NA-L Cut Sheet



Eaton miniature circuit breaker, current-limiting, 2A, 240 VAC / 96 VDC, 3-pole, D curve, thermal magnetic, 10kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-D2-3-NA-L>

Technical Specifications

Brand	Eaton
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	2A
Voltage Rating	240 VAC / 96 VDC
Number of Poles	3

Trip Curve	D curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 240 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	FAZ-D2/3-NA-L

Agency Approvals

UL Listed File #	E235139
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	204453
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FAZ-D2-3-NA-L.pdf>
See store item page for other formats.