

# FAZ-D32-1-NA-SP Cut Sheet



Eaton miniature circuit breaker, current-limiting, 32A, 277 VAC / 48 VDC, 1-pole, D curve, thermal magnetic, 10kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FAZ-D32-1-NA-SP>

## Technical Specifications

|                      |                   |
|----------------------|-------------------|
| Brand                | Eaton             |
| Item                 | Circuit breaker   |
| Circuit Breaker Type | Miniature         |
| Circuit Type         | Feeder and branch |
| Current-Limiting     | Yes               |
| Amperage Rating      | 32A               |
| Voltage Rating       | 277 VAC / 48 VDC  |
| Number of Poles      | 1                 |

|                          |                  |
|--------------------------|------------------|
| Trip Curve               | D curve          |
| Trip Type                | Thermal magnetic |
| Interrupting Rating      | 10kA @ 277 VAC   |
| UL Rating                | UL 489 listed    |
| Mounting                 | 35mm DIN rail    |
| HACR Rated               | Yes              |
| Reverse Feed Capable     | Yes              |
| Manufacturer Part Number | FAZ-D32/1-NA-SP  |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E235139                                |
| UL Recognized File # | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 204453                                 |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FAZ-D32-1-NA-SP.pdf>  
See store item page for other formats.