

# FC-3RLY4 Cut Sheet



Limit alarm, current, voltage input, (4) SPST relay output, 24 VAC/VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal block(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-3RLY4>

## Technical Specifications

<b>Item</b>	Limit alarm
<b>Field Configurable</b>	Yes
<b>Input Current Signal Range</b>	0 - 20 mA
<b>Input Voltage Signal Range</b>	0 - 15 VDC, 0 - 30 VDC
<b>Relay Configuration</b>	(4) Form A (SPST) relays
<b>Load Current</b>	5A at 250 VAC, 5A at 30 VDC
<b>Operating Voltage</b>	24 VAC/VDC
<b>Indicating Type</b>	LED indication
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail or panel
<b>Terminal Block Type</b>	Removable screw terminal block(s)

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>