

FC-3RLY4 Cut Sheet



AutomationDirect limit alarm, current or voltage input, (4) SPST relay output, 24 VAC/VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal block(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-3RLY4>

Technical Specifications

Brand	AutomationDirect
Item	Limit alarm
Field Configurable	Yes
Input Current Signal Range	Input current signal range(s) of 0 - 20 mA
Input Voltage Signal Range	Input voltage signal range(s) of 0 - 15 VDC, 0 - 30 VDC
Relay Configuration	(4) Form A (SPST) relays
Load Current	5A at 250 VAC, 5A at 30 VDC
Operating Voltage	24 VAC/VDC
Indicating Type	LED indication
Housing Material	Plastic
Mounting	35mm DIN rail or panel
Terminal Block Type	Removable screw terminal block(s)

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FC-3RLY4.pdf>
See store item page for other formats.