

FC-P3 Cut Sheet



Signal conditioner, isolated, potentiometer input, current or voltage output, 24 VAC/VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-P3>

Technical Specifications

Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Input Potentiometer Resistance	100-100k Ohms
Output Current Signal Range	0-20 mA and 4-20 mA
Output Voltage Signal Range	0-10 VDC and 0-5 VDC
Operating Voltage	24 VAC/VDC
Housing Material	Plastic
Mounting	35mm DIN rail or panel
Electrical Connection	Removable screw terminal plugs

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document