

FDME-00-1A Cut Sheet

AchieVe photoelectric sensor, tubular, threaded, metal housing, through-beam emitter, infrared, 4m sensing distance, 10-30 VDC operating voltage, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FDME-00-1A>

Technical Specifications

Brand	AchieVe
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	12mm diameter x 55mm body
IP Rating	IP67
Housing Material	Metal
Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC
Number of Wires	3

Sensing Distance	4m
Sensitivity	Potentiometer
Light Emission (NP)	Infrared
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	PVC
Connection	Pigtail
Conductor Size	24 AWG
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FDME-00-1A.pdf>
See store item page for other formats.